

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010099](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Crimp Contact Insert, Female, 25-Pole, 10A, for Turned or Stamped Crimp Contacts, Size 16A «66x16»

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size 16A «66X16»
 Component Type Inserts - Crimp Contact
 Exclude SD Check Yes
 Insert Series S-D
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard CSA C22.2 NO. 182.3, EN 175301-801, EN 60664-1, EN 61984, UL 1977
 UPC 887191870175

Physical


Durability (mating cycles max) 500
 Flammability UL 94V-0
 Gender Female
 Insert Color Grey
 Material - Insert Polycarbonate
 Net Weight 35.000/g
 Number of Rows 3
 Packaging Type Bag
 Polarized to Mating Part Yes
 Poles 25
 Temperature Range - Operating -40°C to +125°C

Electrical

Current - Maximum per Contact 10.0A
 Voltage - Maximum 250V

Material Info

Engineering Number 7125.4012.0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[93601](#) Series

Mates With

[93601-0094](#) Male Crimp Contact Insert

Use With

Turned Contacts - Female