



## AP\* Series Contacts

PART NUMBER: APK -PB25A25-002

[View Line Drawings](#)

<b>Product Family</b>	Transportation
<b>Product Group</b>	APK
<b>Component</b>	Contact
<b>For Connector Style</b>	APK
<b>Contact Size</b>	APK25
<b>Contact Length</b>	29,40 (1.157)
<b>Crimp Size</b>	25
<b>Finish</b>	Tinned, 2µm
<b>Quantity</b>	Reels/3000
<b>Terminal Plating</b>	Gold
<b>Gender</b>	Pin
<b>Contact Resistance</b>	2,50 milliohms
<b>Current Rating</b>	30 A at 55°C with max. wire size
<b>Test Voltage</b>	1050 V RMS
<b>Contact Material</b>	Copper Alloy
<b>Crimp Termination Wire Size</b>	2,50 - 1,50 (.00388 - .00233)
<b>Individual Sealing</b>	Yes
<b>Insulation Ø</b>	2,90 - 2,00 (.114 - .079)
<b>Footnote</b>	Dimensions are shown in mm (inch)



