


ART.: 8630661453410

SL630 AB PRISM



Art.: 8630661453410, SL630 AB, Prismenstruktur, 40W, 4000K, Driver static, 1274mm, Symmetrical - direct, White, LED surface-mount luminaire for interior, comprising: Housing made of steel sheet, die-cast aluminium end caps, powder painted / Prismatic cover for efficient light diffusion, glare reduction and a high level of uniformity / Renovation version with luminaire width > 370 mm to cover existing holes / Direct light distribution / LED Sidelight-Technology for a homogenous light distribution over the entire area of the cover / Colour rendering index Ra > 80 / Colour tolerance according to MacAdam = 3 SDCM / Light engine can be replaced by means of a slide-in mechanism / VDU application suitable acc. to EN 12464-1 (see table) / Special colour versions available upon request

Connected load	40 W
Luminous flux	4730 lm
Efficiency	118 lm/W
Colour temperature	4000K
Colour rendering (CRI)	80
IP class	20
Nominal voltage	220 – 240 V
Colour	WH-RAL9016
UGR	16,3
Glare control	✓

