

## Isoline DALI


### ISOLINE 3380MM 4K DASY DA 8C

### 0042538



#### Product features

- Isoline LED linear DALI dimmable luminaire for industrial and commercial applications. 3380 mm length with double asymmetrical optics provide homogenous light distribution for wide, shelf areas. Suitable for DALI Dimming. Aluminium housing, RAL 9016. Max + 35 °C operating temperature range, 4000 K, CRI 80, UGR <25, 3 SDCM. 112 W power consumption, 16600 lm luminous flux, 147 lm/W efficacy, 3380 mm x 62 mm x 59 mm (L x W x H) dimensions, IP20, IK03, DC 50/60 Hz, Class I. Lifespan L70:B50 60,000 hours.



#### PRODUCT OVERVIEW

Product name	ISOLINE 3380MM 4K DASY DA 8C
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Suspended
Fixture rating	Enclosed
General application	Logistics & Industry
ETIM Class	EC000986
Warranty	5 years
Fixture luminous flux (lm)	16600
Luminous flux (lm)	16500
Luminaire efficacy (lm/W)	147
Colour temperature (K)	4000
Colour Code	840
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 25
Photobiological Risk Group	RG1
Total power consumption (W)	112
Electrical protection	Class I
Control gear type	LED driver constant current
Dimmable	Yes
Dimming method	DALI
Minimum dimming level (%)	1
LED Flickering Rate	Ultra low (5% or less)
Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP20
IK rating	IK03
Product EAN number	5410288425382

#### DATA TABLE

## Isoline DALI

ISOLINE 3380MM 4K DASY DA 8C

0042538

### General data

Product name	ISOLINE 3380MM 4K DASY DA 8C
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Suspended
Fixture rating	Enclosed
General application	Logistics & Industry
Operating temperature range (°C)	0°C...+35°C
ETIM Class	EC000986
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	16600
Luminous flux (lm)	16500
Luminaire efficacy (lm/W)	147
Colour temperature (K)	4000
Colour Code	840
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 25
Photobiological Risk Group	RG1

### Electrical data

Total power consumption (W)	112
Mains voltage (V)	220-240V
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	5.5
Electrical protection	Class I
Control gear required	No
Control gear type	LED driver constant current
Dimmable	Yes
Dimming method	DALI
Minimum dimming level (%)	1
Drive current (mA)	250
Inrush Current (A)	28
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	C
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	Ultra low (5% or less)
Max. Luminaires per 10A B Breaker	14
Max. Luminaires per 16A B Breaker	23

### Lifetime data

Lifespan L70 B50	60000
Lifespan L80 B10	60000
Lifespan L90 B10	31500

## Isoline DALI

ISOLINE 3380MM 4K DASY DA 8C  
0042538


### Physical data

Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP20
IK rating	IK03
IK rating of sensor	IK03
Diffuser finish	Transparent
Diffuser material	PMMA Acrylic
Nominal Product Length (mm)	3380
Nominal Product Width (mm)	62
Nominal Product Height (mm)	59
Weight (kg)	5.0

### Packaging

Single packaging type	Mix(80% carton, 20% plastic)
Product EAN number	5410288425382
Packaging single length / height (cm)	353.0
Packaging single width (cm)	6.5
Packaging single depth (cm)	5.8
DUN14 (outer)	05410288425382
Units per outer package	1
Packaging outer length / height (cm)	354.0
Packaging outer width (cm)	7.0
Packaging outer depth (cm)	6.3

## PHOTOMETRY



## TECHNICAL DRAWINGS

