

Solid carbide end mill

4 cutting edges, TiAlN-coated

ORION[®]

Application:

End mill for universal machining of non-ferrous metals.

Execution:

- solid carbide ultra-fine grain
- straight shank in accordance with DIN 6535 HA
- TiAlN-coated
- centre cutting
- with edge protection chamfer



Art. no.	16827 120
Brand	ORION
Manufacturer Part Number	16827 120
Cutting material	SC
Surface	TiAlN
Type	W
Number of cutting edges	4 PCS
Twist angle	45°
Tool holding device	HA parallel shank
Construction length	Normal
Cutting edge diameter	12 mm
Cutting edge length	26 mm
Length	83 mm
Edge protection chamfer length	0.2 mm
Shank diameter	12 mm
fz aluminium	0.06 mm
Gross Weight	0.124 kg
Overall stainless steel suitability	2
fitness not iron total	1
fitness Titan/Nickel/Super total	2
Product Group	154

EAN

4039247455478