

DTFN steel boring bar, negative left

For longitudinal turning with TN indexable insert

WIDIA 

Application:

For longitudinal turning with TN indexable insert, 60°

Execution:

- Precision-manufactured steel boring bar, internal cooling, type T, pitch angle 90°, tip angle 60°, clearance angle 0°

Advantage:

- Three-edge geometry lowers cost per cutting edge
- Negative body geometry ensures good stability and absorption of force for large cutting depths



Art. no.	17684 010
Brand	WIDIA
Manufacturer Part Number	5696260
ISO name	A 25 R DTFN R/L 16
Min. bore diameter	32 mm
Shank diameter	32 mm
Length	200 mm
Programming size	17 mm
Suitable for indexable inserts	TN.. 1604..
Tool design	Left
Gross Weight	0.656 kg
Product Group	1XG

EAN

4050841470315