

## Precision pointer micrometer

MAHR 40 F



### Application:

For quick testing of parts from series production.

### Version:

- Adjustable tolerance marks
- carbide-tipped measuring faces
- Movable measuring probe for lifting the anvil

### Delivery:

in case



<b>Art. no.</b>	<b>31472 025</b>
<b>Min./max. length measuring range</b>	25-50 mm
<b>Indicating calliper measuring range</b>	+/- 0,065 mm
<b>Digit increment, micrometer</b>	0.01 mm
<b>Digit increment, indicating calliper</b>	0.001 mm
<b>Micrometer error limit</b>	0.002 mm
<b>Indicating calliper error limit</b>	0.001 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Spindle clamping</b>	Yes
<b>Measurement force</b>	9 N
<b>Measuring surface diameter</b>	7.5 mm
<b>Calibration Group</b>	AN
<b>DIN</b>	863

### EAN-Code

4059192004255