

## Precision pointer snap gauges

Marameter



### Application:


For precise testing of cylindrical parts in series.

### Version:

- Carbide measuring faces
- Spring-mounted anvil
- Consistent, repeatable measuring force
- Forged steel bracket
- Measuring and counter probe made from stainless, hardened steel
- Adjustable centring stop

### Delivery:

In wooden box, display unit not included



<b>Art. no.</b>	<b>31936 150</b>
<b>Min./max. length measuring range</b>	150-200 mm
<b>Measuring surface diameter</b>	12 mm
<b>Measurement force</b>	7.5 N
<b>Shaft diameter</b>	8 mm
<b>Spindle clamping</b>	Yes

### EAN-Code

4059192017637