

Assembly trolley with CLIP-O-FLEX hook-on system

With 6 trays incl. 100-piece tool assortment in 6 hard foam inserts

CLIP-O-FLEX®

Application:

The flexible, modular CLIP-O-FLEX system allows the assembly trolley to be set up as required for production, assembly, development or training, and adapted to individual work sequences at any time. CLIP-O-FLEX sets your work/storage area or your organisation system with one clip and at the same time gives the highest level of horizontal and vertical flexibility.

Version:

- Solidly welded sheet steel structure with painted multiplex panel, 30 mm stark
- Workbench panel with CLIP-O-FLEX support rails installed on the top of the housing left, right and at the rear
- With convenient pull-out system incl. CLIP-O-FLEX trays with hook-in angles 0/40/80°
- Incl. 6 ATORN hard foam inserts, made of polyethylene (PE), two-tone black/blue, resistant to most oils and chemicals thanks to closed-cell structure
- 6 ATORN hard foam inserts fitted with 100 ATORN tools, filling 6 tool trolley trays
- Central locking with cylinder lock incl. 2 keys
- Chassis with 2 fixed wheels and 2 guide rollers, diameter 100 mm, with one guide roller with stop

Advantage:

- Simply remove the trays from the cabinet and hang on the hook-in rails at the side
- Flexible hook-on system with only one hooking movement
- Ergonomic workplace design thanks to different inclines and can be relocated horizontally
- Quick access to work equipment, very clear overview
- Rapid conversion and replacement, highest possible level of mobility, less walking required, optimum use of space



Art. no.	50237 199
Number of drawers	2 PCS
Pullout type	Full extension
Height	958 mm
Width	474 mm
Depth	405 mm
Draw width (inner dimension)	365 mm
Drawer depth (inner dimension)	294 mm
Load-carrying capacity per drawer	35 kg
Central locking	Yes
Lock type	Cylinder lock
With sliding handle	Yes
Load-carrying capacity	550 kg
Dynamic load-carrying capacity	225 kg
Number of fixed rollers	2 PCS
Number of steering rollers	2 PCS
Material of wheel	Solid rubber
Wheel diameter	100 mm
Material	Sheet steel
Body colour	White aluminium RAL 9006
Colour of front	Jet black RAL 9005
Surface	Powder-coated