

## swivel hoist ring, quality class 8

Screwed attachment point with ball bearing

CARTEC

### Application:

Screw-on, rotating attachment point for lifting heavy loads that need to be rotated or turned. Suitable for safe lifting in accordance with Machinery Directive 2006/42/EC.

### Version:

- quality class 8 - compact, lightweight design, with DGUV certification
- with ball bearing for easier loading, loadable in all directions
- Can be rotated by 360°, swivel range of bracket max. 180°
- Red, powder-coated surface
- permanent rotation under full load not permitted

### Advantage:

- 4-way safety in every load direction
- constructed, tested and certified according to GS-OA 15-04 - EN 1677

### Delivery:

Carrying capacities up to 35 t and other dimensions deliverable upon request.



<b>Art. no.</b>	<b>77236 020</b>
<b>Thread dimension</b>	M20
<b>Load-carrying capacity</b>	2000 kg
<b>Internal width</b>	34 mm
<b>Bracket diameter</b>	16 mm
<b>Interior height</b>	57 mm
<b>Width of support plate</b>	50 mm
<b>Distance between lower edge of retainer holder and screw head</b>	61 mm
<b>Distance between lower edge of retainer holder and retainer</b>	131 mm
<b>Effective thread length</b>	30 mm
<b>Width across flats</b>	40 mm
<b>Colour</b>	Red

### EAN-Code

8013429800092