



L = 1.0 m : 20 87 146 9001 100
 L = 2.0 m : 20 87 146 9001 200

* If a different length is required, contact your local HARTING office for part numbers and support.

PIN-OUT

MALE INSERT	CABLE	FEMALE INSERT
PIN 1	#1 (BLACK)	PIN 1
PIN 2	#2 (BLACK)	PIN 2
PIN 3	#3 (BLACK)	PIN 3
PIN 4	#4 (BLACK)	PIN 4
PIN 5	#5 (BLACK)	PIN 5
PIN 6	#6 (BLACK)	PIN 6
PIN 7	#7 (BLACK)	PIN 7
PIN 8	#8 (BLACK)	PIN 8
PIN 9	#9 (BLACK)	PIN 9
PIN 10	#10 (BLACK)	PIN 10
PIN 11	#11 (BLACK)	PIN 11
PIN 12	#12 (BLACK)	PIN 12
PIN 13	#13 (BLACK)	PIN 13
PIN 14	#14 (BLACK)	PIN 14
PIN 15	#15 (BLACK)	PIN 15
PIN 16	#16 (BLACK)	PIN 16
PE	GREEN/YELLOW	PE

Notes:
 1. Contacts use crimp style termination.

DESCRIPTION	REV	DATE	NAME	HARTING PART NUMBER
				20 87 146 9001 L00
				DESCRIPTION
				UL2237 Cable Assembly Han 16 E, top-entry, 2-lever
RELEASED FOR PRODUCTION	A	10/16/15	ERW	DRAWING NUMBER
PRELIMINARY RELEASE	-	08/03/15	WOODWORTH	20871469001L00
Standard HARTING tolerances apply unless otherwise specified.				REFERENCE
This drawing is property of HARTING Manufacturing Inc. No exploitation or transfer of information contained herein is permitted without written consent / agreement of HM.				UL2237 ASSEMBLIES
				SHEET 1/1
				REVISION
				A

D
C
B
A