

**Connecting elements  
H4,0/18D GR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



- supplied loose in polybag
- DIN colour code
- other colour code

**General ordering data**

Type	H4,0/18D GR
Order No.	<a href="#">9019190000</a>
Version	Wire-end ferrule, insulated, 12 mm, 10 mm, grey
GTIN (EAN)	4008190141349
Qty.	500 pc(s).
Packaging	loose

## Data sheet

### Connecting elements H4,0/18D GR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	18 mm	Width (inches)	0.709 inch
Net weight	0.26 g		

### Technical data

Version	insulated
---------	-----------

### Wire-end ferrules

Collar diameter (D2)	4.8 mm	Colour code	DIN
Conductor cross-section	4 mm <sup>2</sup>	Contact surface diameter (D1)	2.8 mm
Contact surface length (L2)	10 mm	L1 in mm	18 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 019 A
Plastic collar thickness (S2)	0.3 mm	Stripping length	12 mm
Wire connection cross section AWG, max.	AWG 12		

### Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

### Approvals

Approvals



ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**Connecting elements  
H4,0/18D GR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

---

