






© 1980 年 日本エー・エム・ピー株式会社
AMP 社の諸製品は特許又は特許出願中

© 1980 BY AMP (Japan) Ltd.
ALL RIGHTS RESERVED. AMP
PRODUCTS COVERED BY PATENTS
AND/OR PATENTS PENDING



寸法公差は 0.20
(TOLERANCE: ±0.2)
パネル取付穴 (DIMENSION OF PANEL)



- NOTES:
- 1, APPLIED CONTACT P/N: 170359, 170360, 17361, 170362
 - 2, MATING CONN: PLUG HOUSING P/N 172341
 - △ PANEL THICKNESS: 0.8 ~ 2.0 mm
 - 4, PRESS DIRECTION OF PANEL MUST BE SAME AS HOUSING INSERTED DIRECTION.
 - 5, INSTRUCTION SHEET: IS - 105J
 - 6, PRODUCT SPEC: 108 - 5151
 - △ 7, OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

- 注:
1. 使用端子型番は 170359, 170360, 170361, 170362
 2. 嵌合相手ハウジング型番は 172341.
 - △ 適用パネル厚 0.8 ~ 2.0 mm
 4. 取付穴打抜方向とハウジングの挿入方向は同じとする.
 5. 取扱説明書: IS-105J
 6. 適用製品仕様書: 108-5151

△ 7	OBSOLETE	黄 (YELLOW)	1	172333	-4
		黒 (BLACK)	1-		-9
	△ 7	青 (BLUE)	1-		-6
	OBSOLETE	緑 (GREEN)	1-		-5
		赤 (RED)	1-		-2
		自然色 (NATURAL)		172333	-1
		色 (COLOR)			型番 (P/N)

A2	ECO-10-000444	KK	AEG	JAN 10
A1	黄色追加 J-10297	T.O	M.S	9/28
A	変更 J-9972	A.K	M.S	8/31
0	変更 J81-5998	T.S	Z.T	4/21
0	作成 J81-5987	K.Y	Z.T	3/6
LTR.	変更 (REVISION RECORD)	DR.	CHK.	DATE

材料 (MATERIAL) 6/6 ナイロン (UL94V-2) (NYLON 6/6 UL94V-2)	一般公差 TOLERANCE ± 0.3 EXCEPT ± 1.0 AS NOTED	AMP 日本エー・エム・ピー株式会社 TOKYO, JAPAN
仕上 (FINISH) 色: 表参照 HOUSING COLOR: SEE TABLE	DR. K. yama 2/28 CHK. A. taniguchi 4/21 81 DE. APP.	名称 (NAME) MINI-UNIVERSAL MATE-N-LOK CONN CAP HOUSING 12 Pos. (UL94V-2) 12 極 ミニユニバーサル X 12 極 ロック コネクタ キャップハウジング (UL94V-2) SIZE B LOC J 番号 (NO.) C-172333
	尺度 (SCALE) 2:1	REV. A2 SHEET #

単位: 概 DIMENSIONS IN MM DO NOT SCALE PRINT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[172333-1](#)