

**M8 male 0° with cable**


PVC 3x0.25 ye UL/CSA 0,3m


M8

Male straight

3-pole

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Product may differ from Image

### Approvals



\* only for products with UL/CSA approved cable

### Form

08001

### Technical Data

|                               |                                                                  |
|-------------------------------|------------------------------------------------------------------|
| Operating voltage             | max. 60 V AC/DC                                                  |
| Operating current per contact | max. 4 A                                                         |
| Locking of ports              | Screw thread M8 × 1 mm (recommended torque 0.4 Nm) self-securing |
| Protection                    | IP67 inserted and tightened (EN 60529)                           |

### Cables

|                             |                          |
|-----------------------------|--------------------------|
| Cable number                | 010                      |
| No./diameter of wires       | 3 × 0.25 mm <sup>2</sup> |
| Wire isolation              | PVC (br, bl, bk)         |
| Jacket Color                | yellow                   |
| Shore hardness outer jacket | 85 ± 5A                  |
| Material (jacket)           | PVC (UL/CSA)             |

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

|                            |                |
|----------------------------|----------------|
| Outer diameter             | approx. 4.5 mm |
| Bend radius (fixed)        | 5 × outer Ø    |
| Bend radius (moving)       | 10 × outer Ø   |
| Temperature range (fixed)  | -30...+80 °C   |
| Temperature range (mobile) | -5...+80 °C    |

**Commercial data**

|                        |          |
|------------------------|----------|
| country of origin      | DE       |
| customs tariff number  | 85444290 |
| minimum order quantity | 1        |