



COMPENSATOR FOR REMOTE SWITCH 5TT41..
FOR GLOW LAMP CURRENT 20MA

Model		
product brand name		SENTRON
Latching relay design		others
Voltage		
Continuous voltage fuse version		Yes
Protection class		
Protection class IP		IP20, with connected conductors
Switching capacity		
Switching capacity current		
<ul style="list-style-type: none"> at cos phi 0.6 	A	16
Control current		
Control voltage frequency		
<ul style="list-style-type: none"> _1 / initial value 	Hz	50
<ul style="list-style-type: none"> _1 / Full-scale value 	Hz	50
Number		
Number of terminals		2
Mechanical Design		
Mounting height	mm	90
mounting position		any
Installation depth	mm	70
Number of width units		1
Mounting type		DIN rail

Environmental conditions

Ambient temperature

• minimum	°C	-10
• maximum	°C	40
• with relative humidity 95% / acc. to DIN 50015	°C	35

Certificates

General Product Approval



[other](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5TT4920>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5TT4920/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=5TT4920

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015