

Star Knobs 5334 Stainless Steel

Material: Stainless steel 1.4301 (AISI 304). Grip drawn from stainless-steel sheet. Hub butt-welded on, blasted, matt finish.




Version C = with blind hole d_3^{H7} .

Version E = with tapped blind hole d_2 .

Refined and cost-saving manufacturing techniques led to this cost-efficient stainless steel-version.

Ordering Details: e.g.: Product No. 661 993 01, Star Knob Stainless Steel, Drawn, 40 mm



| Product No. Vers. C | Product No. Vers. E | d_1 mm | Thread d_2 mm | Bore d_3^{H7} mm | d_4 mm | h_1 mm | h_2 mm | t min. mm | Weight g |
|------------------------|------------------------|-------------|--------------------|-----------------------|-------------|-------------|-------------|--------------|-------------|
| 661 993 01 | 661 993 11 | 40 | M8 | 8 | 14 | 24 | 12 | 15 | 37 |
| 661 993 03 | 661 993 13 | 50 | M10 | 10 | 18 | 31 | 17,5 | 18 | 65 |
| 661 993 05 | 661 993 15 | 60 | M12 | 12 | 20 | 39 | 21 | 22 | 107 |


Star Knob Screws 5334 Stainless Steel

Material: Stainless steel 1.4301 (AISI 304). Grip drawn from stainless-steel sheet. Hub butt-welded on, blasted, matt finish.




Refined and cost-saving manufacturing techniques led to this cost-efficient stainless steel-version.

Ordering Details: e.g.: Product No. 661 993 01, Star Knob Screw Stainless Steel, 40 mm



| Product No. | d_1 mm | d_2 mm | l mm | d_3 mm | h_1 mm | h_2 mm | Weight g |
|-------------|-------------|-------------|---------|-------------|-------------|-------------|-------------|
| 661 993 41 | 40 | M8 | 20 | 14 | 24 | 12 | 50 |
| 661 993 42 | 40 | M8 | 30 | 14 | 24 | 12 | 55 |
| 661 993 43 | 40 | M8 | 40 | 14 | 24 | 12 | 57 |
| 661 993 44 | 50 | M10 | 20 | 18 | 30 | 16,5 | 91 |
| 661 993 45 | 50 | M10 | 30 | 18 | 30 | 16,5 | 97 |
| 661 993 46 | 50 | M10 | 40 | 18 | 30 | 16,5 | 101 |
| 661 993 47 | 60 | M12 | 30 | 20 | 37,5 | 20 | 155 |
| 661 993 48 | 60 | M12 | 40 | 20 | 37,5 | 20 | 162 |
| 661 993 49 | 60 | M12 | 50 | 20 | 37,5 | 20 | 170 |



Reworking within
24h-service possible.
Custom made parts
on request.