

9 pc. Tamper Resistant Torx® Bit Set 16030

- Set includes: (8) Tamper resistant, durable S2 steel Torx bits, sizes: TR8, TR10, TR15, TR20, TR25, TR27, TR30 and TR40
- (1) 1/4 inch drive adapter
- Includes bit holder



UPC	Master	Inner
8-02090-16030-1	60	10

26 pc. Ratcheting Precision Screwdriver 16092

- Set Includes: (1) 5" Ratcheting Driver, (1) 4-1/2" Extension Bar, (7) Phillips: PH000, (2) PH00, (2) PH0, PH1 and PH2, (5) Slotted: 1/16", 5/64", 3/32", 1/8" and 5/32", (5) SAE Hex: 1/16", 5/64", 3/32", 1/8" and 5/32", (5) Star: T5, T6, T7, T8 & T9, (2) Triwing: 2mm and 3mm
- For use with a wide range of projects including automotive, small engine, household & electronic applications
- Aluminum constructed 4-3/4 in. bit driver
- Comfort grip handle



UPC	Master	Inner
8-02090-16092-9	96	12

26 pc. Precision Bit and Driver Set 16028

- One-click release
- Rotatable tool tray
- Push button ejection
- Color coded ring for easy identification
- Specialized tip for smart phones
- Bits include: (4) Phillips: 000, 00, 0, 1; (2) Pentalobe: TS1, TS5; (5) Slotted: 1.0, 1.5, 2.0, 2.5, 3.0; (7) Hex: 0.7, 0.9, 1.3, 1.5, 2.0, 2.5, 3.0; (6) STAR: T4, T5, T6, T7, T8, T9; (1) Magnetic bit holder; (1) 3-1/4 in. Aluminum Bit Driver

UPC	Master	Inner
8-02090-16028-8	48	12



Precision Pocket Screwdriver

- Star bits for specialty applications
- Convenient bit storage in handle and handy pocket clip
- Anodized aluminum alloy handle is knurled for a secure grip
- Magnetic tip holds bits securely

Part #	Sizes	UPC	Master	Inner
17201	Slotted: 1/16, 5/64, 3/32, 1/8 inch Phillips: #000, #00, #0, #1	8-02090-17201-4	48	6
17202	Star: T3, T4, T5, T6, T7, T8, T9, & T10	8-02090-17202-1	48	6

