

PETG 3D Filament

For 3D Printers



Description

PETG Filament that combines the advantages of ABS and PLA.

Features

- No smelling while printing
- Low shrinkage
- Low hygroscopic
- Good toughness

Specification

Print temperature : 230°C to 250°C
Bed temperature : 25°C to 80°C
Print speed : 30 to 80mm/s

Part Number Table

Description	Colour	Part Number
PETG Filament, 1.75mm, 1kg/roll	Natural	MC011464
	Solid Black	MC011465
	Solid Red	MC011466
	Solid White	MC011467
	Solid Orange	MC011468
	Solid Green	MC011469
	Solid Grey	MC011470
	Solid Gold	MC011471
	Solid Silver	MC011472
	Solid Blue	MC011473
	Solid Yellow	MC011474
	Solid Purple	MC011475

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of Premier Farnell Limited 2019.

www.element14.com
www.farnell.com
www.newark.com

