

# Han B Protect Cover for Hood PG29



Part number	09 30 024 5442
Specification	Han B Protect Cover for Hood PG29
HARTING eCatalogue	https://b2b.harting.com/09300245442

Image is for illustration purposes only. Please refer to product description.

#### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> B
Type of accessory	Protection cover
Description of the accessory	for hoods Metal
	With fixing cord

### Version

Size	24 B
Locking type	Double locking lever (on the hood)

# **Technical characteristics**

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

## Material properties

Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

Page 1 / 2 | Creation date 2023-12-01 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com Product data sheet 09 30 024 5442 Han B Protect Cover for Hood PG29



## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)
Specifications and approvals	
Approvals	DNV GL
Commercial data	
Packaging size	1
Net weight	79.3 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140048027
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors