

Roller container

With 1 storage area and 5 fully-extending drawers

Execution:

- Welded sheet steel structure
- Deposit tray equipped with a ribbed rubber mat
- Tilt-proof due to built-in individual drawer pull-out lock
- 4 wheels with rubber tyres
- For suitable insert materials for drawers, see from no. 50485 060-265 and no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010

Advantage:

- The roller container can be pushed under workbenches with a clearance height of 800 mm



Art. no.	50284 233
Brand	HK
Manufacturer Part Number	50284233
Number of drawers	5 PCS
Pullout type	Full extension
Number of loading surfaces	1 PCS
Drawer front height	1 x 60 mm, 1 x 90 mm, 2 x 120 mm, 1 x 150 mm
Height	790 mm
Width	570 mm
Depth	680 mm
Drawer width (inner dimension)	450 mm
Drawer depth (inner dimension)	600 mm
Load-carrying capacity per drawer	70 kg
With single pull-out safety brake	Yes
Central locking	Yes
Lock type	DOM® locking system
With sliding handle	Yes
Load-carrying capacity	400 kg
Number of fixed rollers	2 PCS
Number of steering rollers	2 PCS
Number of wheel adjusters	2 PCS
Material of wheel	Solid rubber
Wheel diameter	100 mm
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Gross Weight	77.000 kg
Product Group	501

EAN

4053625403295