



RGB led dimmer module

12-24VDC
common anode
RGB
or
single colour led
strips



12-24VDC power supply
e.g. Velleman LPS series



Easy DIN-rail
mounting



Pushbuttons



Features

- Easy DIN-rail mounting
- Hi-power outputs
- Dual pushbutton operation:
 - Press to select colour
 - Press to adjust intensity
- Buttons can be paralleled
- Single colour option
- Short circuit protection

Technical

Input voltage: 12-24VDC
 Max output current: 3x5A
 PWM freq: 90Hz
 DIN-rail enclosure: 2 modules wide

