



5x20mm fused terminal blocks

Product overview

- GWIT to 775°C and GWIF 850°C
- 1 - 5 pole terminal strip with 5x20mm fuseholder
- Integral spare fuse carrier
- Interlocking fuseholder with CFTBN/1
- Anti rotation spigot
- IP20 finger protection
- Cable entry 4mm² (2.5mm² with wire protector)
- Wire protector on fuse terminal as standard
- Wire protectors on earth pole to order
- Meets creepage and clearance requirements of IEC (8mm)
-  approved on non earth versions



SPECIFICATION	
Rating	Fuseholder 250V AC Terminal 450V AC
Current rating	Fuseholder 13A Terminal 20A
Moulding	UL94-V0 flame retardant PA
Terminal	Brass, nickel plated
Fuse clip	Phosphor bronze
Wire protector	Stainless steel
Temperature	-20° to 120°C
Fuse size	5x20mm glass or ceramic
Screws	Steel zinc plated M3, 0.5Nm
EN60127	Fuseholders
EN60998	Terminal blocks

PART NO.	BODY DIMENSIONS (L)	FUSE WIRE PROTECTOR	EARTH HOLE	EARTH SCREW WASHERS	EARTH WIRE PROTECTED	WIRE PROTECTED TERMINALS
CFTBN/1	16.1 mm	•				
CFTBN/2	20.6 mm	•				
CFTBN/3	30.8 mm	•	•	•		
CFTBN/4	40.7 mm	•	•	•		
CFTBN/5	50.9 mm	•	•	•		
CFTBN/3NE	30.8 mm	•				
CFTBN/4NE	40.7 mm	•				
CFTBN/5NE	50.9 mm	•				
CFTBN/3NS	30.8 mm	•	•			
CFTBN/4NS	40.7 mm	•	•			
CFTBN/5NS	50.9 mm	•	•			
CFTBN/2WP	20.6 mm	•				•
CFTBN/3WP	30.8 mm	•				•
CFTBN/4WP	40.7 mm	•				•
CFTBN/5WP	50.9 mm	•				•
CFTBN/3EWP	30.8 mm	•	•	•		•
CFTBN/4EWP	40.7 mm	•	•	•		•
CFTBN/5EWP	50.9 mm	•	•	•		•
CFTBN/3EWPg	30.8 mm	•	•	•	•	•
CFTBN/4EWPg	40.7 mm	•	•	•	•	•
CFTBN/5EWPg	50.9 mm	•	•	•	•	•

ACCESSORIES

- Terminal cover
- Screw/dust protection
 - Easily cut to required size



PART NO.	POLES
CFTBN/3NC	3 pole cover
CFTBN/5NC	5 pole cover

ASSOCIATED PRODUCTS

CFB0520F	- Glass 5x20mm quick blow fuses	page 228
CFB0520T	- Glass 5x20mm time delay fuses	page 228
CFB0521CF	- Ceramic 5x20mm quick blow fuses	page 229
CFB0521CT	- Ceramic 5x20mm time delay fuses	page 229

