

M12 MALE 0° SHIELDED WIREABLE SCREW TERM.

5-pol. max.0,75mm² 6-8mm

M12


Male straight

A-coded, 5-pole, shielded


Clamping range cable entry: 6...8 mm

[Link to Product](#)

Illustration



Male



Product may differ from Image

Approvals



Form

13321

Technical Data

Operating voltage	max. 125 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	max. 0.75 mm ²
Sealing range (cable diameter)	6...8 mm
Protection	IP67 inserted and tightened (EN 60529)
Housing	CuZn, nickel plated

General data

Temperature range	-25...+85 °C
-------------------	--------------

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1