

MOSA M12 MALE 0° FIELD-WIREABLE (IDC)

B-cod., 2-pol., 0,25-0,34mm², shielded

M12

Male straight

Field-wireable (IDC terminals)

B-coded, 2-pole, shielded

[Link to Product](#)

Illustration



Product may differ from Image

Technical Data

Operating voltage	max. 32 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.25...0.34 mm ² (AWG 22...24)
Sealing range (cable diameter)	4.5...8.8 mm
Outer wire diameter	2.0...2.6 mm
Protection	IP67 inserted and tightened (EN 60529)

General data

Temperature range	-25...+85 °C
-------------------	--------------

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1