

## MSUD VALVE PLUG FORM A 18MM

PVC 3X0.75 black 1.2m

Form A (18 mm)

0...230 V AC/DC, without components

Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Approvals



### Form

18081

### Technical Data

|                               |  |
|-------------------------------|--|
| Operating voltage             | max. 230 V AC/DC                       |
| Operating current per contact | max. 10 A                              |
| Locking of ports              | M3 (recommended torque 0.4 Nm)         |
| Protection                    | IP67 inserted and tightened (EN 60529) |
| Housing                       | Black plastic (gray on request)        |

### Cables

|                             |                          |
|-----------------------------|--------------------------|
| Cable number                | 616                      |
| No./diameter of wires       | 3 × 0.75 mm <sup>2</sup> |
| Wire isolation              | PVC (bk, num, gnye)      |
| Jacket Color                | black                    |
| Shore hardness outer jacket | 80 ± 5A                  |
| Material (jacket)           | PVC                      |
| Outer diameter              | approx. 5.9 mm           |
| Bend radius (fixed)         | 5 × outer Ø              |
| Bend radius (moving)        | 10 × outer Ø             |
| Temperature range (fixed)   | -30...+70 °C             |
| Temperature range (mobile)  | -5...+70 °C              |

### Commercial data

|                        |          |
|------------------------|----------|
| country of origin      | CZ       |
| customs tariff number  | 85444290 |
| minimum order quantity | 1        |