

SIVACON, side panel, flat, IP40, H: 2000 mm, W: 800 mm, RAL 7035



Figure similar

Model	
Product brand name	SIVACON
Product designation	Side panel/rear panel
Design of the product	Flat
Design of the surface	Powder-coated
Design of the product / EMC version	No
Protection class	
Protection class IP	IP40
Appearance	
RAL color number	RAL 7035
Color	light grey
Product details	
Product component	
• cable entry	No
• Lock	No
Mechanical Design	

Height	2 000 mm
Width	800 mm
Depth	800 mm
Material	steel
Equipment marking	<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 U • acc. to DIN EN 81346-2 UC

EMC	Declaration of Conformity	Test Certificates	other
-----	---------------------------	-------------------	-------

[Miscellaneous](#)



EG-Konf.

[Special Test Certificate](#)

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1080-2UW63-1C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1080-2UW63-1C>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1080-2UW63-1C

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



