


Part Number: 1937135X

Type	Size	Rating	Description
LED	M16	24Vac/dc	Standard Bezel Panel Indicator



Part #	Colour	Current(mA)	Intensity(mcd)
19371350	Red	8/17	1000
19371351	Green	7/15	100
19371352	Yellow	8/17	650
19371357	Blue	7/14	1400
1937135WA	White	6/13	4000

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Luminous intensity at dc
- 3 Storage temperature -25 °C to +80°C
- 4 Application temperature -20 °C to +60°C
- 5 Voltage tolerance ±10%
- 6 Due to component tolerances, colour temperature variations may be observed
- 7 The terminals are not qualified for soldering
- 8 Degree of protection IP67 when used with the supplied gasket
- 9 The plastic(polycarbonate) has limited chemical resistance
- 10 RoHS & REACH SVHC compliant