

Han-Yellock 60 cover for hood high



Image is for illustration purposes only. Please refer to product description.

Part number	11 12 600 5452
Specification	Han-Yellock 60 cover for hood high
HARTING eCatalogue	https://b2b.harting.com/11126005452

Identification

Category	Accessories
Series of hoods/housings	Han-Yellock®
Type of accessory	Protection cover
Description of the accessory	for carrier hoods With fixing cord Thermoplastic

Version

Size	Han-Yellock® 60
------	-----------------

Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	1
Net weight	41 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140192263
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors