

Han B Protect Cover for Hood PG29



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 024 5442
Specification	Han B Protect Cover for Hood PG29
HARTING eCatalogue	https://b2b.harting.com/09300245442

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of hood/housing	Protection cover
Description of hood/housing	for hoods Metal With fixing cord

Version

Size	24 B
Locking type	Double locking lever (on the hood)

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol
ECHA SCIP number	5b0b428a-c671-4c90-9b6d-16804ea5737a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	79.3 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140048027
eCl@ss	27440208 Cap for industrial connectors