

## Han-Yellock 60 cover for hood high



Image is for illustration purposes only. Please refer to product description.

Part number	11 12 600 5452
Specification	Han-Yellock 60 cover for hood high
HARTING eCatalogue	<a href="https://b2b.harting.com/11126005452">https://b2b.harting.com/11126005452</a>

### Identification

Category	Accessories
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Protection cover
Description of hood/housing	for carrier hoods With fixing cord Thermoplastic

### Version

Size	Han-Yellock® 60
------	-----------------

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	1
Net weight	41 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140192263
eCl@ss	27440208 Cap for industrial connectors