

# Han B Base Panel 4 Pegs Metal Cover



Part number	09 30 024 0317
Specification	Han B Base Panel 4 Pegs Metal Cover
HARTING eCatalogue	https://b2b.harting.com/09300240317

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With metal cover
Туре	Low construction

### Version

Size	24 B
Locking type	Double locking lever (on the hood)
Field of application	Standard hoods/housings for industrial connectors

#### Technical characteristics

Limiting temperature	-40 +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR



### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

### Specifications and approvals

Approvale	CE
Approvals	DNV GL

### Commercial data

Packaging size	1
Net weight	171 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140046900
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors