

## Micrometer

Adjustable anvil

Mitutoyo

### Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

### Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Spindle travel 50 mm

### Advantage:

- Sturdy, robust and lightweight construction for large measurement ranges

### Delivery:

Includes box, two setting standards



|   |                  |
|---|------------------|
| <b>Art. no.</b>                         | <b>32016 120</b> |
| <b>Brand</b>                            | MITUTOYO         |
| <b>Manufacturer Part Number</b>         | 105-410          |
| <b>Min./max. length measuring range</b> | 1200-1300 mm     |
| <b>Vernier scale</b>                    | 0.01 mm          |
| <b>Measuring surface diameter</b>       | 8 mm             |
| <b>Measuring spindle increments</b>     | 0.5 mm           |
| <b>Spindle clamping</b>                 | Yes              |
| <b>Error limit</b>                      | 23 µm            |
| <b>Display</b>                          | Nonius           |
| <b>Min./max. measurement force</b>      | 5-10 N           |
| <b>Calibration Group</b>                | D                |
| <b>Gross Weight</b>                     | 40.500 kg        |
| <b>Product Group</b>                    | 3MA              |

### EAN

4946368007588