

Manual pick-up magnet

Permanently high magnetic force

Application:

For the safe manual transport of sheet metal and steel parts.

Version:

- **Ref. no. 010** for thin sheets and small pieces.
- **Ref. no. 020** particularly for medium- and large-sized sheets (most popular model).
- **Ref. no. 030** for thick plates, heavily scaled plates, heavy workpieces.

Advantage:

- Entirely maintenance-free
- Permanently high magnetic force
- No magnetisation of workpieces

| | |
|---|------------------|
| Art. no. | 77350 010 |
| Load-carrying capacity | 120 kg |
| Suitable for min./max. sheet metal thickness | 1-2 mm |
| Surface area length | 140 mm |
| Surface area width | 84 mm |

