

STAF 6 FE -L



Part number	09 70 006 2812
Specification	STAF 6 FE -L
HARTING eCatalogue	https://b2b.harting.com/09700062812

Identification

Category	Inserts
Series	Staf®

Version

Termination method	Solder termination
Gender	Male
Size	3 A
Number of contacts	6
Details	male insert with female contacts

Technical characteristics

Conductor cross-section	2.5 mm ²
Rated voltage	25 V AC 60 V DC
Electrical data acc. to IEC 61984	10 A 25 V 0.8 kV 3
Rated current	10 A
Rated voltage	25 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	50 V
Rated voltage acc. to CSA	50 V
Insulation resistance	≥10 ¹⁰ Ω
Contact resistance	≤2 mΩ
Limiting temperature	-40 ... +100 °C
Mating cycles	≥500

Material properties

Material (insert)	Polyamide
-------------------	-----------



Pushing Performance

Material properties

Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	HB
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	10
Net weight	14.83 g
Country of origin	Romania
Customs tariff number	85366990