



GE
Lighting



Single Ended Halogen

FEL Q1000/4CL 120V

88625

Product information

Quartzline® lamps designed for optimum performance in today's precision range of stage, studio and architectural luminaires. Full range up to 24,000 W
-Range of bases to meet the needs of OEMs -
Chromised seal protection up to 500° C.



Product data

EAN Code	0043168886253
DUN Code	10043168886250
Bulb Shape	Tubular
Bulb Diameter [mm]	18
Cap/Base	G9.5
Gross weight per piece [g]	35
Maximum Overall Length [mm]	104.78
Net weight per piece [g]	25
Brand	General Electric (GE)

Performance data

Nominal power [W]	1000
Nominal lamp voltage [V]	120
Nominal lumens [lm]	27500
Nominal correlated colour temperature (CCT) [K]	3200
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	375
Ballast Required	Yes
Coil type	CC-8
Energy efficiency class (EEC)	C
Light Center Length [mm]	60.5
Weighted energy consumption [kWh/1000h]	1073.66

Logistic data

Pack Quantity	24
Pallet quantity EUR (PC)	4032
Pallet quantity UK (PC)	4800
Inner pack type	BOX
Outer pack type	OUTER BOX
Outer case size	255 x 170 x 130 (mm)
Layer quantity	504 EUR, 600 UK
Layer quantity EUR	504
Layer quantity UK	600
Product status	Available

Application areas



Film and Broadcast



Theatre

Downloads & Links

[Go to the catalog site \(HTTP\)](#)[Entertainment Solution Spectrum Catalogue \(PDF\)](#)[Lighting design tools & calculators \(HTTP\)](#)

Disclaimer

Special Purpose Lamp, Not suited for household illumination