



DIN Built-In Standard Socket

12-24 V, inner-Ø 12 mm, fitting for standard and universal plugs.
With 6.3 mm T-flat plug terminals. Port for installation Ø 18 mm.
Fastening by hexagon nut, panel thickness 2-9 mm. Max. load up to 16 A.
TÜV-certified and monitored. With terminals according to DIN EN ISO 4165.

	BP	SP
	SU = 500	SU = 60
16 A	67607000	67617000



DIN Built-In Standard Socket with cap

12-24 V, dust and splash-proof version, inner-Ø 12 mm, fitting for standard and universal plugs.
With 6.3 mm T-flat plug terminals. Port for installation Ø 18 mm.
Fastening by hexagon nut, panel thickness 2-9 mm. Max. load up to 16 A.
TÜV-certified and monitored. With terminals according to DIN EN ISO 4165.

	BP	SP
	SU = 500	SU = 60
16 A	67607100	67617100



DIN Built-In Standard Socket with mounting plate

12-24 V, inner-Ø 12 mm, fitting for standard and universal plugs.
With 6.3 mm T-flat plug connection. Port for installation Ø min. 26 mm.
Fastening by hexagon nut and enclosed screws, panel thickness 2-9 mm.
Max. load up to 16 A. TÜV-certified and monitored. With terminals according to DIN EN ISO 4165. Dimensions mounting plate L x W x H: 60 x 45 x 2 mm.

	BP	SP
	SU = 500	SU = 60
16 A	67607030	67617030
16 A, with protective cap	67607130	67617130



DIN Built-In Standard Socket metal with protective cap

12-24 V, inner-Ø 12 mm, fitting for standard and universal plugs.
With 6.3 mm T-flat plug terminals. Port for installation Ø 18 mm.
Fastening by hexagon nut, panel thickness 1-10 mm.
Max. load up to 16 A.

	BP	SP
	SU = 100	SU = 60
16 A	53114330	53114321



DIN Built-In Standard Socket, waterproof

12-24 V, with screw cap. Waterproof to IP 67, cables are waterproof encapsulated. Temperature resistant -40° to 105° C, inner-Ø 12 mm, fitting for standard and universal plugs, contacts according to DIN EN ISO 4165.
Assembled with 30 cm cable. Port for installation Ø 18 mm.
Fastening by hexagon nut, panel thickness 1-10 mm. Max. load up to 16 A.

	BP	SP
	SU = 50	SU = 20
16 A	52005000	52005001



Triple Built-In Socket

12-24 V, three standard sockets, inner-Ø 12 mm, fitting for standard and universal plugs. Fastening by enclosed screws.
Cable connection via flat plug 6.3 mm. Max. load up to 16 A.
TÜV-certified and monitored. With contacts according to DIN EN ISO 4165.
Dimensions L x W x H: 93.5 x 33.5 x 2.5 mm.

	BP	SP
	SU = 100	SU = 60
16 A	57612002	57612003