



Bemerkung:

Werkstoff: Polyamid, schwarz
Längentoleranz: 0,10 mm

Art.-Nr.	SW	L	Zoll	C/B	G1/G2
8030-6	6	6		4/8	M3/M3
8030-7	6	7		5/8	M3/M3
8030-8	6	8		5/8	M3/M3
8030-9	6	9		6/8	M3/M3
8030-10	6	10		7/8	M3/M3
8030-11	6	11		8/8	M3/M3
8030-12	6	12		8/8	M3/M3
8030-13	6	13		8/8	M3/M3
8030-14	6	14		10/8	M3/M3
8030-15	6	15		10/8	M3/M3
8030-16	6	16		10/8	M3/M3
8030-17	6	17		10/8	M3/M3
8030-18	6	18		10/8	M3/M3
8030-19	6	19		10/8	M3/M3
8030-20	6	20		10/8	M3/M3
8030-21	6	21		10/8	M3/M3
8030-22	6	22		10/8	M3/M3
8030-23	6	23		10/8	M3/M3
8030-24	6	24		10/8	M3/M3
8030-25	6	25		10/8	M3/M3
8030-26	6	26		10/8	M3/M3
8030-27	6	27		10/8	M3/M3
8030-28	6	28		10/8	M3/M3
8030-29	6	29		10/8	M3/M3
8030-30	6	30		10/8	M3/M3
8030-31	6	31		10/8	M3/M3
8030-32	6	32		10/8	M3/M3
8030-33	6	33		10/8	M3/M3
8030-34	6	34		10/8	M3/M3
8030-35	6	35		10/8	M3/M3

Art.-Nr.	SW	L	Zoll	C/B	G1/G2
8030-36	6	36		10/8	M3/M3
8030-37	6	37		10/8	M3/M3
8030-38	6	38		10/8	M3/M3
8030-39	6	39		10/8	M3/M3
8030-40	6	40		10/8	M3/M3
8030-41	6	41		10/8	M3/M3
8030-42	6	42		10/8	M3/M3
8030-43	6	43		10/8	M3/M3
8030-44	6	44		10/8	M3/M3
8030-45	6	45		10/8	M3/M3
8030-46	6	46		10/8	M3/M3
8030-47	6	47		10/8	M3/M3
8030-48	6	48		10/8	M3/M3
8030-49	6	49		10/8	M3/M3
8030-50	6	50		10/8	M3/M3
8030-55	6	55		10/8	M3/M3
8030-60	6	60		10/8	M3/M3