


Data Sheet

Type Number 341
Designation IEC ---
System Silver oxide / Zinc / Alkaline - Electrolyte



Nominal Voltage 1,55 V
Typical Capacity C 15 mAh
 Load 68,1 kOhm, at 20°C down to 1.2 V

Weight (approx.) 0,28 g
Volume 0,07 ccm
Coding..... Date of Manufacturing Month/Year

Temperature Ranges

	min	max.
Storage	0°C	60°C
Discharge	0°C	60°C

Dimensions

	min	max.
Diameter (Ø).....	7,75	7,90
Height (A/B)	1,3	1,45

Segment Watch

Main Applications Watch
 Photo
 Electronic Devices

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	1.2 V
Continuous 24h/d,7d/w Current [µA]:	68100 Ω	Time:	650 h
		Capacity [mAh]:	15
	23	Energy [mWh]:	23,5