
## Twist Tail™



## No tool needed



### Twist Tail™

# Looking for a cable tie fast and easy to install, without using an extra tool?

#### The new Twist Tail<sup>™</sup> Cable Tie

#### How does it work?

Wrap the Twist Tail<sup>™</sup> cable tie around the bundle of cables, bend the excess tail in two directions and twist! The tail breaks right off, leaving no sharp edges to scratch your hands or your cables.

It's as simple as that.

#### **Features & Benefits**


- New all-plastic cable tie, with unique, patent pending design
- Quick and easy to install, no tools required
- Strong, made of Polyamide 6.6, with 133N minimum tensile strength
- Safe, tail breaks off neat and clean, with no sharp edges
- General purpose applications, indoor and outdoor
- UL recognised
- Available in 3 different lengths and 2 colours (white and UV-resistant black)



#### **Technical Information**

E49405

Material	Polyamide 6.6	
Temperature max.	+85°C	
Colour	White or UV-resistant black	
Flammability rating	UL 94 V-2	
Other properties	Halogen free, Silicone free,	
	UV resistant (black)	







Product Ref.	Colour	Length	Width	Thickness	Max.	Quantity
		[mm]	[mm]	[mm]	bundle diameter [mm]	[pieces]
		[]	[]	[]	[1]	[[0.0000]]
TT-7-30-9-L-EU	white	181	4.7	1.4	45	50
TT-7-30-0-L-EU	black	181	4.7	1.4	45	50
TT-11-30-9-L-EU	white	282	4.7	1.4	76	50
TT-11-30-0-L-EU	black	282	4.7	1.4	76	50
TT-14-30-9-L-EU	white	358	4.7	1.4	102	50
TT-14-30-0-L-EU	black	358	4.7	1.4	102	50

www.tnb-europe.com

