

Product type designation

PROFIBUS bus connector, RS485, Fast Connect, with PG socket, 90°

Product description

PROFIBUS bus connector, RS485, Fast Connect, with PG socket, 90°

SIMATIC DP, BUS CONNECTOR FOR PROFIBUS UP TO 12 MBIT/S 90 DEGREE ANGLE CABLE OUTLET, 15,8 X 72,2 X 36,4 MM (WXHXD), IPCD TECHNOLOGY FAST CONNECT, WITH PG SOCKET



Suitability for use

For connecting PROFIBUS nodes to the PROFIBUS bus cable

Transmission rate

Transfer rate / with PROFIBUS DP

9.6 kbit/s ... 12 Mbit/s

Interfaces

Number of electrical connections

- for PROFIBUS cables
- for network components or terminal equipment

2

1

Type of electrical connection

- for PROFIBUS cables
- for network components or terminal equipment

Integrated insulation displacement contacts for 2-core PB FC installation cables

Sub-D connector (9-pin)

Type of electrical connection / FastConnect

Yes

Mechanical data

Design of terminating resistor

Integrated resistor combination that can be selected with slide switch

Material / of the enclosure

plastic

Design, dimensions and weight

Type of cable outlet

90° cable outlet

Width

15.8 mm

Height

72 mm

Depth

36.4 mm

Net weight	10 g
Permitted ambient conditions	
Ambient temperature	
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
Protection class IP	IP20
Product properties, functions, components / general	
Product property	
• silicon-free	Yes
Product component	
• PG connection socket	Yes
• strain relief	Yes
Standards, specifications, approvals	
Certificate of suitability	
• RoHS conformity	Yes
• UL approval	Yes
last modified:	09.03.2015