

6.01531.00 Power 180-5 W OF

Power Compressor 180-5 W OF

- Compact and mobile piston compressor for flexible use both indoors and at construction sites
- Portable assembly compressor – ideal for tackers and nails as well as for separating pipes by force
- For single phase alternating current
- Oil-free piston sealer: simple transportation and reduced service requirements
- Instrument panel with easy to read manometer for tank- and working pressure
- Working pressure can be regulated according to application by means of a pressure reducer with manometer
- Fittings and control elements protected in tubular frames and clearly visible
- Wind-up mechanism for the cable
- Good cold start feature by means of push button with safety valve
- Overload protection: protects the motor from overheating
- Rubberised feet for optimum stability

Comparative technical values

Suction Rate	160 l/min
Filling Capacity	90 l/min
Effective delivery volume (at 80% max. pressure)	75 l/min
Maximum Pressure	8 bar
Rated Input Power	1,1 kW
Maximum speed	2.850 /min
Tank Capacity	5 l
Sound pressure level (LpA)	81,6 dB(A)
Sound power level	81,6 dB(A)
Dimensions	370 x 395 x 286 mm
Weight	16 kg
Cable Length	4 m

Scope of delivery

1 Universal quick-action coupling