


Part number

CGMA 35



Brief description:

100A CG contacts, silver plated, 35mmq, AWG 2

Product description		Approvals / Standards	
Model	male contacts	Quality mark	 DNV GL, BV, EAC
Version	Crimp contacts CLASS series	Conformity	CQC, CE
Series	100A CG contacts	General ordering information	
Family	crimp contacts	EAN13 code	8015747122719
N. of poles	1 pole	Tariff number	85369095
Technical data		Packaging Information	
Current	100 A	Packaging length	132,00 mm
Wire cross-section	35,00 mm ²	Packaging height	108,00 mm
AWG size	2	Packaging width	210,00 mm
Contact type	silver plated	Packaging weight	3,98 kg
Further technical details		Packaging volume	2,99 dm ³
Weight	23,00 g	Packaging description	Carton box
		Packaging quantity	150 Pcs
		Packaging EAN code	8015747225595
		Sub-packaging length	1,00 mm
		Sub-packaging height	1,00 mm
		Sub-packaging width	1,00 mm
		Sub-packaging weight	0,80 kg
		Sub-packaging description	Plastic box
		Sub-packaging quantity	30 Pcs
		Sub-packaging EAN barcode	8015747122740

Part number

CGMA 35



Catalogue drawings

CGF and CGM

