


- **Probe and Housing** with Vent Holes **Around Element**
- ✓ Temperature Range: -100 to 250°C (-148 to 500°F)
- ✓ M12, 4-Pin, A-Coded Plug Connector for **Easy Installation**
- Available With or Without **NPT Mounting Threads**
- Probe Will Withstand 400 psi (27.6 bar) Differential Pressure **Between Airstream and Ambient Conditions**

This sensor combines the usefulness of our ultra-precise air measurement RTD sensors with the convenience of our PR-21 M12 enabled RTD sensors. The design of the probe includes a perforated sheath over the sensing element shielding it from debris while allowing airflow to directly reach the element. This results in a sensor which is capable of providing accurate, fast responding temperature measurements.


OMEGA also offers a wide variety of compression fittings, extension cables and measurement and control instruments which allow you to fully customize the system to best méet your measurement and control needs.







Order a M12 Extension
Cable to Easily Connect
Your Sensor to Your **Instrumentation**





PR-25AP-A-1200-0-M12, shown with M12C-SIL-4-R-F-1.5.

Model Number	Probe Diameter	Probe Length	Mounting Thread
PR-25AP-A-0600-0-M12	1/4"	6"	No thread
PR-25AP-A-1200-0-M12	1/4"	12"	No thread
PR-25AP-A-1800-0-M12	1/4"	18"	No thread
PR-25AP-A-0600-1/2-M12	1/4"	6"	½ NPT
PR-25AP-A-1200-1/2-M12	1/4"	12"	½ NPT
PR-25AP-A-1800-1/2-M12	1/4"	18"	½ NPT
PR-25AP-A-0600-3/8-M12	1/4"	6"	% NPT
PR-25AP-A-1200-3/8-M12	1/4"	12"	% NPT
PR-25AP-A-1800-3/8-M12	1/4"	18"	% NPT
PR-25AP-A-0600-1/4-M12	1/4"	6"	½ NPT
PR-25AP-A-1200-1/4-M12	1/4"	12"	½ NPT
PR-25AP-A-1800-1/4-M12	1/4"	18"	½ NPT

Note: option 1 wiring standard.

For option 2 wiring add "-2" to end of model number, no additional charge.

For $\frac{1}{3}$ DIN accuracy, change "-**A-**" to "-**1/3-**" after the "-**25AP-**" in the model number for an additional cost. For $\frac{1}{10}$ DIN accuracy, change "-**A-**" to "-**1/10-**" after the "-**25AP-**" in the model; number for an additional cost.

A limited selection of Pt1000 elements are available, please consult sales.

Ordering Examples: PR-25AP-A-0600-A-M12, Pt100, Class A RTD sensor with 1/4" diameter by 6" long probe, M12 connection with no mounting

PR-25AP-1/10-1200-1/2-M12, Pt100, Class 1/10 DIN RTD sensor with 1/4" diameter by 12" long probe, M12 connection with 1/2 NPT mounting threads.