NYS231LL

3 pole 3.5 mm plug, with x-large cable outlet, metal handle



Technical Information

Product	
Title	NYS231LL
Electrical	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current	depends on mated connector
Contact resistance	depends on mated connector
Mechanical	
Cable O.D.	8 mm
Lifetime	1000 mating cycles
Environmental	
Flammability	Complies with IEC 68-2-20
Temperature range	-25 °C to +70 °C