



Product Construction Conductor

30 AWG (Solid) Silver Plated Copper Wire Conductor OFHC

Applications

Hook-Up wire
Point to point wiring
Printed circuit board wiring

Industry Approvals

UL Style 1423
RoHS Compliant

Specifications

Gauge : 30 AWG
Strands : Silver Plated Copper Wire (Solid)
Insulation Type : PVDF (Polyvinylidene Fluoride)
Nominal Insulation Wall : 0.004 in.
Nominal O.D. : 0.02 in.
Insulation Temperature : -40°C to +105°C

Part Number Table

Description	Colour	Reel length	Part Number
PVDF Insulated Solid Silver-Plated Copper Hook-Up Wire, 30 AWG	Black	50 ft. (15.24m)	24-1820
	Red		24-1810
	Yellow		24-1850
	Green		24-1830