
PRODUCT-DETAILS

FLT0510

LT-T FLEXIBLE CONDUIT 25MM 10M



General Information

Extended Product Type	FLT0510
Product ID	7TCA297020R0183
EAN	5011949214866
Catalog Description	LT-T FLEXIBLE CONDUIT 25MM 10M
Long Description	Liquid Tight, Low Fire Hazard Conduit, Nominal Conduit Size 25mm, 3/4 Inch US Trade Size, Outside Diameter 26.4mm, Inside Diameter 21.0mm, Static Bend Radius 110mm, Reel Length 10 Meters, Galvanised Steel Core, String Packing with LFH Covering, Black

Ordering

EAN	5011949214866
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	12.68 lb 5.751 kg
--------------------	----------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Indoors / Outdoors, Marine, Buildings, & Rail Infrastructure Where Low Smoke and Toxicity are of Concern
Brand / Label	Kopex
Color	Black
Flexibility	Medium
Inside Diameter	21.0 mm
Material	Galvanized Steel Core with String Packing and Low Fire Hazard Coating
Nominal Size	3/4 in NC25
Number of Batteries	0
Outside Diameter	26.4 mm
Product Name	flex metal conduit
Product Type	Liquid Tight Low Fire Hazard Conduit
Radius	110 mm
Standards	BSI Kitemark KM-90009, Low Voltage Directive, London Underground I-085, NFF16-101 (I1 F1)
UPC	786210276816

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	FLT0510
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	FLT0510

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

