

Han 10M-Metal Cover-Bolt-for Base



Part number	09 37 010 5405
Specification	Han 10M-Metal Cover-Bolt-for Base
HARTING eCatalogue	https://b2b.harting.com/09370105405

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han [®] M
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings for cable to cable housing Metal With fixing cord
Version	
Size	10 B
Locking type	Double locking lever
Technical characteristics	
Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12
Material properties	
RoHS	compliant

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

Page 1 / 2 | Creation date 2023-12-01 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL
Commercial data	
Packaging size	1
Net weight	5 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140055551
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors