

META CLIP boltless rack with shelves

Load capacity per bay 100/230 kg, plastic coated



Application:

Universal rack system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools.

Execution:

- Double-row boltless rack with pre-assembled frame = clinched frame
- Both rows securely connected on the back
- Shelves height-adjustable, spacing 25 mm
- Shelves with a 50 mm hole grid to accommodate accessories
- Basic rack planning dimensions: Nominal length + 56 mm, 2 x nominal depth + 75 mm

Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



Art. no.	50167 468
Brand	META
Manufacturer Part Number	200176593
Height	2000 mm
Length	1056 mm
Depth	636 mm
Nominal length	1000 mm
Nominal depth	600 mm
Design	Shelving unit
Type of assembly	To insert
Surface	Plastic-coated
Design of the frame	Pre-assembled
Grid dimension	25 mm
Number of shelves	5 PCS
Load-carrying capacity per shelf	150 kg
Load-carrying capacity per field	1650 kg
Number of frame	2 PCS
Quality label	RAL-RG 6 14/ 1
Made in	Germany
Gross Weight	70.614 kg
Product Group	508

EAN

4026212282092