

Workbench, series WGS with undercounter cabinet

Solid beechwood 2000 mm, 4 drawers with partial extension, 1 door

Execution:

- Solidly welded steel sheet construction
- Left: Undercounter cabinet with drawers and door
- Right: base made of square steel tube 45 x 45 x 2 mm, with level compensation
- Door opening angle 180°
- Delivered fully assembled

Advantage:

- When you buy this product, you plant a tree and also receive a tree certificate!
- When you buy this product, you plant a tree and also receive a tree certificate!



Art. no.	50212 156
Number of drawers	4 PCS
Working height	850 mm
Worktop width	2000 mm
Pullout type	Partial extension
Worktop height	50 mm
Colour of front	Anthracite grey RAL 7016
Worktop depth	700 mm
Cabinet colour	Light grey RAL 7035
Adjustable in height	No
Drawer surface	0.27 m ²
Surface	Powder-coated
With single pull-out safety brake	Yes
Load-carrying capacity	800 kg
Lock type	DOM® locking system
Drawer front height	1 x 60 mm, 2 x 90 mm, 1 x 120 mm
Drawer width (inner dimension)	450 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	450 x 600 mm
Material of worktop	Solid beech
Drawer depth (inner dimension)	600 mm
Load-carrying capacity per drawer	100 kg
Material of base frame	Steel plate
Central locking	Yes
Levelling	Yes
Product Group	Prod. Gr. 5BC

EAN

4053625402540