

## swivel hoist ring, quality class 8

Screwed attachment point with ball bearing

CARTEC

### Application:

Screw-on, rotating attachment point for lifting heavy loads that need to be rotated or turned. Suitable for safe lifting in accordance with Machinery Directive 2006/42/EC.

### Version:

- quality class 8 - compact, lightweight design, with DGUV certification
- with ball bearing for easier loading, loadable in all directions
- Can be rotated by 360°, swivel range of bracket max. 180°
- Red, powder-coated surface
- permanent rotation under full load not permitted

### Advantage:

- 4-way safety in every load direction
- constructed, tested and certified according to GS-OA 15-04 - EN 1677

### Delivery:

Carrying capacities up to 35 t and other dimensions deliverable upon request.



|  |                  |
|--|------------------|
| <b>Art. no.</b>  | <b>77236 036</b> |
| <b>Thread dimension</b>  | M36              |
| <b>Load-carrying capacity</b>  | 8000 kg          |
| <b>Internal width</b>  | 50 mm            |
| <b>Bracket diameter</b>  | 23 mm            |
| <b>Interior height</b>   | 95 mm            |
| <b>Width of support plate</b>  | 85 mm            |
| <b>Distance between lower edge of retainer holder and screw head</b> | 95 mm            |
| <b>Distance between lower edge of retainer holder and retainer</b>   | 205 mm           |
| <b>Effective thread length</b>                                       | 54 mm            |
| <b>Width across flats</b>  | 75 mm            |
| <b>Colour</b>  | Red              |

### EAN-Code

8013429800382